

CXL Educational Microscope

Configuration

Binocular

	Item	Specifications
	Stand	Sturdy stand with convenient location of focus controls
	Viewing Body	Binocular tube, 45° inclined, 360° rotatable
	Eyepiece	Wide field eyepiece 10x/18mm with eyeguard.withanti fungus coating
-	Nosepiece	Quadruple Nosepiece , with ball bearings
	Objectives	EP series DIN Semi Plan Achromatic objectives 4x:10x 40x (spring loaded), 100x (spring loaded, oil) with anti fungus coating
	Stage	Mechanical stage 135×125 mm with low drive co-axial control. Ball bearing slides with graduated scale. SS holder for slide 75×50 mm movement.
	Focusing	Coaxial coarse and fine focusing system with ball bearing guideways
	Condenser	ABBE condenser N.A. 1.25 with aspheric lens. Iris diaphragm with snap in blue filter
	Illumination	6V/20W halogen with variable electronic intensity control.
	Electrical	Input 220V - 240V AC
		9:



Configurations

Description

Halogen Standard, 20W